

Label sheet, DIN A4 - BMKL 18X 8 WH CUS - 0824244

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Label sheet, DIN A4, can be ordered: Sheet, white, labeled according to customer specifications, Mounting type: Adhesive, Lettering field: 18 x 8 mm



The figure shows a version of the article

Why buy this product

- ✓ The unperforated SK U ... sheets are available for custom label designs
- ✓ These labels have been specially developed for laser printers
- ✓ Labeling service: Phoenix Contact can custom-label all BMKL ... markers according to your requirements
- ✓ Can be printed on all commercially available laser printers



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 351195
Weight per Piece (excluding packing)	9.0 g
Custom tariff number	39199000
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	18 mm
Width (a)	8 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 80 °C
---------------------------------	------------------

General

Color	white
Base element material	Polyester
Components	Silicone-free

Label sheet, DIN A4 - BMKL 18X 8 WH CUS - 0824244

Technical data

General

Material	Polyester
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	288
Number of individual labels per row	9
Marking mounting type	Adhesive

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137

ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410