

Features

- Cooling Fan
- Increases soft starts / stops per hour to 40 @ Trip Class 10

RS PRO VMX-agility External Fan Size 1

RS Stock No.: 206-045



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO VMX-agility External Fan size 1

- Used on 206-096, 206-098, 206-099, 206-101, 206-102, 206-103, 206-105
- Allows up to 40 starts / stops per hour at Trip Class 10
- The fan operates automatically during a soft start or soft stop and will continue to run if the heatsink temperature is $> 45^{\circ}\text{C}$. The fan stops when the heatsink temperature has fallen below 40°C

General Specifications

Device Type	Fan
Function	Soft-Starter cooling
Voltage	24V
Dimensions	H220mm x W91mm x D39mm
Weight	220gm
Fixing Type	Screw

Approvals

Standards	CE, UL, cUL
Legislation	<p>Directives:</p> <p>2014/35/EU - Electrical equipment designed for use within certain voltage limits [Low Voltage Directive - LVD].</p> <p>2014/30/EU - Electromagnetic compatibility [EMC]</p> <p>2011/65/EU - Restriction of the use of certain hazardous substances in electrical and electronic equipment [RoHS] and amending Commission Delegated Directive (EU) 2015/863 with effect from 22 July 2019.</p> <p>Harmonised Standards:</p> <p>EN 60947-4-2:2012 - Low Voltage switchgear and controlgear. Part 4: Controlgear and motor-starters. Section 2. AC Semiconductor motor controllers and starters.</p> <p>EN IEC 63000: 2018 - Technical documentation for the assessment of electrical and electronic products with respect to RoHS.</p>
Environmental	Products comply to RoHS and REACH