

Features

- Type of Fiber: OM4 Duplex
- SC Connector
- Tight Optical Cable
- OM4: IEC IEC 60793-2-40
- SC Connector: IEC 61754-4
- Diameter: 3X6mm

RS PRO Patch 50 OM4 3x6 mm Aqua SC Dx/PC-SC Dx/PC 5,00 m

RS Stock No.: 0794548



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Multimode patchcords are used to connect high speed and legacy networks like Gigabit Ethernet, Fast Ethernet and Ethernet. The multimode patchcords are manufactured using LSZH cables which conform to IEC, EIA TIA and Telecordia standards. The OM4 patchcords are terminated with a standard connector which gives optimum optical performance.

General Specifications

Communication Channels	Duplex
Connectors	SC Dx
Fibre Type	OM4, ITU-651, TIA/EIA 492AAAA
Colour	Aqua

Technical Specifications

Diameter	3x6 mm
Operating Temperature	-20 to +60°C
Core Diameter	50/125 µm
Duplex	Assemblies available with clips (SC)
Sheath Material	Low Smoke Zero
Cable Material	LSZH
Strength Member	Aramid
Splitting Length	250 mm

Optical Specifications

Return Loss	>45 dB
Tensile Strength Cable Retention	>50N
Low Insertion Loss	<0.3 dB

Approvals

Declarations	MFR Declaration of Conformity
Hazardous Area Certification	Conforms to TIA/EIA 492AAAA, IEC60793-2-10 A1b
Standards Met	REACH, RoHS & SvHC materials compliant

Similar Products

Stock No.	Brand	Product Name
0794545	RS PRO	Patch 50 OM4 3x6 mm Aqua SC Dx/PC-SC Dx/PC 2,00 m
0794546	RS PRO	Patch 50 OM4 3x6 mm Aqua SC Dx/PC-SC Dx/PC 3,00 m
0794549	RS PRO	Patch 50 OM4 3x6 mm Aqua SC Dx/PC-SC Dx/PC 10,00 m