



Cut



Heat



Light Duty

Lightweight cut-resistant industrial gloves with exceptional grip

- **Enhanced grip:** ANSELL GRIP™ Technology and palm coating make for industrial gloves with significant grip performance
- **Heightened defenses:** HyFlex® 11-541 industrial gloves feature INTERCEPT™ Cut Resistance Technology, providing ANSI/ISEA 105-2024 CUT A4 and EN ISO D protection
- **Advanced comfort:** ZONZ™ Comfort Fit yarn and stitching enhance these HyFlex® gloves' comfort, while reducing hand fatigue
- **Reinforced durability:** HyFlex® 11-541 safety gloves achieve EN and ANSI/ISEA 105-2024 ABRASION LEVEL 4 thanks to FORTIX™ Abrasion Resistance Technology
- **Added dexterity:** The 11-541's ultralight liner blends personal protection with optimized flexibility
- **Aesthetics and convenience:** These PPE gloves' dirt-masking palm hides stains and they are offered in vend pack form



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Utilities
- Warehousing

Applications

- Handling metal sheets & panels
- Handling parts with sharp, rough edges
- Final assembly
- Handling materials with sharp or rough edges

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-541

Palm coated with INTERCEPT TECHNOLOGY® and ANSELL GRIP™ Technology

Key Features

- **ANSELL GRIP™ Technology:** For strong, confident grip
- **INTERCEPT™ Cut Resistance:** ANSI/ISEA 105-2024 CUT A4 and EN ISO D hand protection
- **ZONZ™ Comfort Fit:** For PPE gloves offering comfort and dexterity

Vulcanization Chemical Accelerators

- Zinc Dibutyldithiocarbamate
- Zinc 2-mercaptobenzothiazole

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Technologies

 **ANSELL GRIP™**
Ansell Grip Technology

 **FORTIX™**
Abrasion Resistance Technology

 **INTERCEPT™**
Cut Resistance Technology

Kevlar®



Touchscreen Compatible

 **ZONZ™**
Comfort Fit Technology

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



4X21D

EN 407



X1XXXX

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-541	Finishing: Palm Coated Coating Material: Foam Nitrile Liner Material: Kevlar®, Nylon, Spandex, Stainless steel Cuff Style: Knitwrist	18	6, 7, 8, 9, 10	196-250 mm; 7.71-9.84 inches	Grey	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

Ansell