

# **ENGLISH**

## **Datasheet**

Stock No: 437-3706

## RS Pro 2000mm Long Unthreaded Stainless Steel Pipe, 8mm Nominal Outer Diameter 0.6mm



Image representative of range

### **Product Details**

#### Metric Tube

A range of RS Pro stainless steel 316L tubing in 2 m lengths. Available in a range of diameters from 6 mm to 12 mm.

#### Features and Benefits

- Supplied in 2 m lengths
- · Straight ends
- · Maximum working pressure 75 bars
- Maximum operating temperature 600°C

#### Compression Fittings - Stainless Steel

#### Compression Fittings - Stainless Steel

Compression fittings suitable for use with a variety of tube materials including stainless steel, PTFE, semi-rigid nylon and polyurethane. Maximum working pressure is 80 bar (1160 psi) and maximum working temperature is 250°C at working pressure. The fittings can also be used for industrial vacuum applications. They come complete with sleeve nuts and olives., Welded 316L Stainless Steel (ASTM A312)

# **Specifications:**

Nominal Outer Diameter	12mm
Length	2000mm
Wall Thickness	1mm