

M18 FHS20-552

M18 FUEL™ HATCHET™ PRUNING SAW 20 CM

- M18 FUEL™ HATCHET™ pruning saw delivers outstanding power and torque to cut hardwood without bogging down
- Designed to meet the ergonomic, performance, and durability needs of landscape maintenance professionals
- Compact design for increased control and maneuverability in tight access areas
- Up to 180 cuts in 10 x 10 cm cedar on a full M18™ HIGH OUTPUT™ 5.5 Ah battery charge for outstanding productivity
- Easy access chain tensioner ensures quick adjustment to chain tension
- Variable speed trigger gives the user full control over the power range
- All metal bucking spikes allow for increased leverage during applications
- Automatic oiler for ease of use and proper chain lubrication
- Onboard storage for scrench
- The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™

Chain bar length (cm)	20
Chain speed (m/s)	5.0
Chain pitch (mm ")	9.5 / 3/8"
Chain gauge (mm ")	1.1 / 0.043"
Weight with battery pack (EPTA) (kg)	3.1 (M18 HB5.5)
Kit included	2 x M18 HB5.5 Battery packs, M12-18 FC Charger, No kitbox or bag supplied
Article number	4933480118

