

M18 BLDDRC-502C

M18™ COMPACT BRUSHLESS DRILL DRIVER

- Compact brushless drill driver measuring 145 mm in length for access into tight spaces
- Advanced 13 mm heavy duty metal chuck for quick bit changes and superior bit retention
- 60.5 Nm of torque - best power to size ratio
- All metal reversible belt clip to hang your tool quickly and easily
- On board fuel gauge and LED light
- Brushless motor, REDLITHIUM™ battery pack and REDLINK™ electronic deliver power, run time and durability
- Flexible battery system: works with all MILWAUKEE® M18™ batteries
- Optimised speed for faster drilling & fastening (0 - 550/ 0 - 1700 rpm)



REDLITHIUM™



No load speed (rpm)	0-550/ 0-1700
Chuck capacity (mm)	13
Max. drilling wood/ steel/ masonry (mm)	52/ 13/ 16
Max. torque (Nm)	61
Weight with battery pack (EPTA) (kg)	1.5 (M18 B5)
Kit included	2 x M18 B5 Battery packs, M12-18 C Charger, Kitbox
Article Number	4933492835