

Q 1,5/4A10/24-M20KU-ESA BK PE - Panel feed-through



1584787

<https://www.phoenixcontact.com/in/products/1584787>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Panel feed-through with wire exit 1.5 mm² and 0.1 m litz wire: connecting thread: M20, 4-pos.

Your advantages

- Innovative and time saving - QUICKON fast connection for time saving of up to 80 % for on-site connection
- Robust throughout: housing with IP65/IP67 protection for a wide range of applications
- Safer connection with mechanical coding to protect against mismatching, and touch-proof protection in accordance with DIN EN 0105
- Efficient - by using panel feed-throughs, devices no longer need to be opened in order to connect cables

Commercial data

Item number	1584787
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	BF6
Product key	AF6HAB
Catalog page	Page 476 (C-2-2019)
GTIN	4046356149617
Weight per piece (including packing)	29.92 g
Weight per piece (excluding packing)	29.92 g
Customs tariff number	85444290
Country of origin	PL

Q 1,5/4A10/24-M20KU-ESA BK PE - Panel feed-through



1584787

<https://www.phoenixcontact.com/in/products/1584787>

Technical data

Product properties

Product type	Panel feed-through
Number of positions	4
Position marking	1, 2, 3, 4
Number of connections	4

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Connection data

Connection technology

Connection method On the device side	Single wires (10 cm long; 1.5 mm ²)
Frequency of connections between conductors of the same cross section	max. 10 (if the conductor is connected more than once, seal and cap may need to be replaced.)

Conductor connection

Conductor cross section flexibel	0.75 mm ² ... 1.5 mm ²
Conductor cross section solid	0.75 mm ² ... 1 mm ²
Connection cross section AWG	18 ... 16
Tightening torque Union nut	3 Nm
Tightening torque Contact carrier	4.5 Nm
Tightening torque Locking nut	4.5 Nm
Wrench size Union nut	19 mm
Wrench size Contact carrier	24 mm

Pin assignment

Contact Color (signal designation) Contact (optional)	1 BK
	2 BN
	3 BU
	4 GNYE

Dimensions

Dimensional drawing	
Width	24 mm
Height	24 mm
Length	55.9 mm

Electrical properties

Q 1,5/4A10/24-M20KU-ESA BK PE - Panel feed-through



1584787

<https://www.phoenixcontact.com/in/products/1584787>

Rated surge voltage (II/2)	6 kV
Rated surge voltage (III/2)	6 kV
Rated surge voltage (III/3)	6 kV
Rated current	15 A
Contact resistance	< 3 mΩ
rated voltage (II/2)	1000 V (with insulating sleeve)
rated voltage (III/2)	800 V (with insulating sleeve)
Rated voltage (III/3)	500 V
Nominal voltage U_N	500 V AC
	500 V DC
Nominal current I_N	17.5 A

Material specifications

Color	black (RAL 9005)
Material Housing	PA
Material Contact	CuZn
Material Contact surface	tin-plated
Flammability rating according to UL 94	V0
Material wire insulation	PVC / PE

Cable/line

Cable length	0.1 m
Structure of individual litz in acc. with VDE 0295 / smallest wire diameter	VDE 0295 class 1 to 6/min. 0.15 mm
External cable diameter	6 mm ... 12 mm
Wire diameter including insulation	1.8 mm ... 3 mm
Position marking	1, 2, 3, 4
Material wire insulation	PVC / PE

Mounting

Mounting type	Front mounting M20
Assembly note	If the conductor is reconnected, it must be cut off above the last contact point. QUICKON components may only be operated when under no load.

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
Impact strength	IK07
Ambient temperature (operation)	-40 °C ... 80 °C
	-25 °C ... 50 °C
Temperature when conductor connected	-5 °C ... 50 °C


Q 1,5/4A10/24-M20KU-ESA BK PE - Panel feed-through

1584787


<https://www.phoenixcontact.com/in/products/1584787>

Drawings

Dimensional drawing



Diagram



Q 1,5/4A10/24-M20KU-ESA BK PE - Panel feed-through



1584787
<https://www.phoenixcontact.com/in/products/1584787>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1584787>

**EAC**
Approval ID: RU C-DE.A*30.B.01102

	VDE approval of drawings Approval ID: 40032336			
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
	500 V	-	-	0.75 - 1.5

Q 1,5/4A10/24-M20KU-ESA BK PE - Panel feed-through



1584787

<https://www.phoenixcontact.com/in/products/1584787>

Classifications

ECLASS

ECLASS-11.0	27440602
ECLASS-13.0	27440602
ECLASS-12.0	27440602

ETIM

ETIM 9.0	EC002566
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

Q 1,5/4A10/24-M20KU-ESA BK PE - Panel feed-through



1584787
<https://www.phoenixcontact.com/in/products/1584787>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	3.605 kg CO2e

Q 1,5/4A10/24-M20KU-ESA BK PE - Panel feed-through



1584787

<https://www.phoenixcontact.com/in/products/1584787>

Accessories

Q-MU M20 - Nut

1640702

<https://www.phoenixcontact.com/in/products/1640702>

Nut (plastic) to lock the contact carrier from the inside of the device



Q-PROT13/16 - Filler plug

1670222

<https://www.phoenixcontact.com/in/products/1670222>

Closing caps, for Pg13/ Pg16, for closing unoccupied connections



Q 1,5/4A10/24-M20KU-ESA BK PE - Panel feed-through



1584787

<https://www.phoenixcontact.com/in/products/1584787>

PT/FS 4,8 - Insulating sleeve

1670497

<https://www.phoenixcontact.com/in/products/1670497>



Insulating sleeve, as touch protection, for 4.8 mm slip-on sleeves, slide onto the conductor before

MICROFOX-SB - Diagonal cutter

1212489

<https://www.phoenixcontact.com/in/products/1212489>



Electronic diagonal cutter, round head, without chamfer, with opening spring, mirror-polished and oiled, 2-component grip, cutting capacity: soft 0.2 - 2.0 mm; medium hard 1.2 mm; hard 0.5 mm diameter

Q 1,5/4A10/24-M20KU-ESA BK PE - Panel feed-through



1584787

<https://www.phoenixcontact.com/in/products/1584787>

QSS 19 - Socket wrench

1670895

<https://www.phoenixcontact.com/in/products/1670895>



Socket wrench, for tightening and unscrewing the QUICKON union nut, wrench size 19 mm

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in