


# **FEATURES**

- Good generalpurpose insulation for 'light' environments. Waterproof and very flexible
- Flat pair construction
- ANSI colour coded
- The American
   National Standards
   Institute (ANSI)
   coordinates U.S.
   standards with
   international
   standards so that
   American products
   can be used
   worldwide.

# RS PRO Thermocouple & Extension Wire Type Vx PVC Insulated Flat Pair Thermocouple Cable / Wire (ANSI) 7/0.2mm 50m (164ft)

RS Stock No.: 2154937



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

# Thermocouple & Extension Wire



# **Product Description**

Compensating cable resembles the thermoelectric characteristic of the relevant thermocouple over a limited ambient temperature range, 0° to 80°C typically. Since these cables are made from low cost materials, cost savings can be achieved on plant installations compared with running true thermocouple extension cable.

# **General Specifications**

General Description	Good general-purpose insulation for 'light' environments. Waterproof and very flexible.				
Cable Length	50m (164ft)				
Cable Type	Flat pair construction				
Core / Strands	7/0.2mm				
Conductor Cross Section 7/0.2 (mm2)	0.219				
Outer Colour	Red				
+ Colour	Brown				
- Colour	Red				
Drain Wire	No				
Insulation Material	PVC Insulated				
Loop Resistance 7/0.2 (Ohms per combined metre)	2.3				
Max. Temperature	+105°C (+221°F)				
Min. Temperature	-10°C (+14°F)				
+ Conductor	Copper				
- Conductor	Constantan				
Screen	No				
Standards Met	Colour code (cores & jacket) to ANSI MC96.1				
Thermocouple Type	Compensating type Vx (KCB) for type K Thermocouples				
Tolerance	Class 2				

# **Approvals**

RoHS Compliant	Yes
I •	

# **Similar Products**

Туре	Cable	Core / Strands	10m (32.8ft)	25m (82ft)	50m (164ft)	100m (328 ft)	200m (656 ft)
Vx	PVC	7/0.2mm	2154936	8140103	2154937	8140112	8140115



RS Components is a leading provider for Automation and Control Gear, below is a selection of best selling products:





# Temperature. It matters



# **Thermocouples**

Including exposed junctions with fitted or moulded miniature plug and insulated leads, ideal for test and development applications. 1, 2, 3, 5 & 10m lengths available

in IEC or ANSI colours.



Thermocouple & PRT Cable

Thermocouple cables are available in IEC or ANSI colour codes. Insulation types include PFA, PTFE, PVC & Fibreglass. Available spool lengths include 10, 25, 50, 100 and 200m.

# **Best Sellers**



ANSI Type K Exposed Junction RS 814-0134 Allied 70656459


**ANSI Type K High** 




**IEC Type K** Exposed Junction RS 363-0250



# **Best Sellers**







#### Calibration

Whether it's existing equipment or a new purchase, you need to have confidence in the accuracy of your measurements.

That's where our calibration service can help.

Purchase new products with confidence.

A certificated calibrated sensor straight out of the box,

# ready to use.

#### **RTD Detectors**

Wire-wound type provides greater accuracy and stability but are vulnerable to shock.

Flat film type are resistant to shock and have quicker thermal response times.

Various lengths and diameters available, in class A, B and 1/10th Din.



#### **Fabricated and Specialist** Thermocouples

Styles include; Magnet, Washer, Nozzle, Leaf, Bayonet & Bolt thermocouple. Various lengths and calibration types available.

# **Best Sellers**



ANSI SYSCAL Type K Mineral Insulated Thermocouple RS 181-7296



IEC SYSCAL Type K Mineral Insulated Thermocouple RS 181-7288



# **Best Sellers**



PT1000 Thin Film Detector RS 362-9907 Allied 70643582

PT100 Wire **Wound Detector** RS 611-7839 Allied 70646151



# **Best Sellers**



Magnet Thermocouple RS 762-1115 Allied 70651739



**Heavy Duty** Thermocouple RS 762-1128 Allied 70651743



**Rubber Patch** Thermocouple RS 290-5036 Allied 70642886

## **Best Sellers**



IEC Thermocouple Plug RS 455-9764 Allied 70644391



ANSI Thermocouple RS 769-1127 Allied 70652125



**IEC Thermocouple PCB Socket** RS 381-7570 Allied 70643749



### Thermocouple Connectors

Range of miniature or standard thermocouple connectors. Available in thermocouple types K, J, T, E, N, RS, B, and copper. IEC, ANSI & JIS colour codes available.



RS Components is a leading provider for Automation and Control Gear, below is a selection of best selling products:

