

Store 'n' Click USB 3.2 Gen 1 Drive

Data is just a click away with the Verbatim Store 'n' Click USB drive! The Store 'n' Click USB gives you the ability to capture all your data in one small, convenient location and move that information with you throughout the day, whether you're at home or at the office.

The unique 'slide and lock' design allows you to easily extend and retract the USB connector, protecting it when not in use. It locks into position when using the drive and clicks back into a closed position when not in use. The other benefit being that there is no cap to lose!

The USB 3.2 Gen 1 interface provides data transfer speeds of up to 5Gbps. It is also backwards compatible with USB 2.0 ports* so can be used in a wide variety of existing devices without needing to upgrade.

Available in a range of colour and capacity combinations:

49306 = 16GB x 3 (Red, Blue and Yellow)

49307 = 32GB x 1 (Black)

49308 = 32GB x 2 (Red and Blue)



Store 'n' Click USB 3.2 Gen 1 Drive

PN	Capacity	Bar code	EAN128 code	EAN14 code
49306	16GB	0 23942 49306 8	(02) 00 023942 49306 8 3715 91806	50023942 49306 3
49307	32GB	0 23942 49307 5	(02) 00 023942 49307 5 3710 91806	50023942 49307 0
49308	32GB	0 23942 49308 2	(02) 00 023942 49308 2 3710 91806	50023942 49308 7

Product Dimensions:	53mm x 22mm x 10mm (L x W x H)
Product Weight:	9g
Pack Dimensions:	90mm x 11mm x 135mm (W x D x H)
Pack Weight:	49306 = 36g/ 49307 = 18g/ 49308 = 27g
Packs per Carton:	49306 = 15 & 49307/ 49308 = 10
Carton Dimensions:	95mm x 73mm x 140mm (W x H x D)
Carton Weight:	249 grams
Cartons per Pallet:	840
Layers per Pallet:	7
Units per Pallet:	12,600

System requirements:

USB 3.2 Gen 1 host port (backwards compatible with USB 2.0)

Windows 10, 8, 7 or higher

Mac OS X 10.4 or higher

Languages:

Front of pack: English (product descriptor in French on the back)

Back of pack:

English, French, Germany, Italian, Spanish, Portuguese, Polish, Russian, Czech, Hungarian, Croatian, Slovakian, Simplified Chinese and Korean