



Fuse-link, low voltage, 800 A, AC 415 V, 80 kA, BS88/J, 73 x 129 mm, gL/gG, BS, 92 mm fixing centres

Part no. 800A 415V AC TYPE J FUSE
Catalog No. 800SJ28

Similar to illustration

Delivery program

Product range			Fuse
Basic function			Utility fuse-link
Field of application			low voltage
Rated current	I	A	800
Rated voltage			AC 415 V
Construction size			BS88/J
Size			73 x 129 mm
Utilization category			gL/gG
Description			92 mm fixing centres
Breaking Capacity		kA	80
usable for size/applications			feeder pillars
Standard/Approval			BS
Shape			dual bolted tags
Standards/Regulations			BS88-2 IEC 60269-2
Optional accessories			fuse-holder JW4

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			Other
Rated current		A	800
Rated voltage		V	415
Voltage type			AC
Rated switching capacity		kA	80
Utilization category			Other
Type of fuse status indicator			None
Insulated metal gripping lugs (IMGL)			No