

Features

- Tough polyester tension cords provide high tensile strength and low stretch.
- Temperature resistance from -70°C to +70°C.
- State of the art design

RS PRO V & Wedge Belts

RS Stock No.:

173-9977,173-9978,173-9979,173-9980,
173-9981,173-9982,173-9983,173-9984,
173-9985,173-9986,173-9987,173-9988



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Wrapped Classical V and High Performance Wedge Belts are designed and built for exceptionally reliable and durable performance on all industry standard drives. A rubber impregnated fabric cover protects the belts' inner components and ensures excellent oil, ozone and abrasion resistance. Specially compounded rubber construction promotes dimensional stability, static conductivity. Manufacture ensures that Classical and High Performance Wedge Belts deliver an efficient and cost effective drive solution with a comprehensive range of over 800 sizes available from stock in the UK.

General Specifications

RS Stock Number	Description	Datum Length
1739977	SPA SECTION WRAPPED WEDGE BELT 1132MM L	1132
1739978	SPA SECTION WRAPPED WEDGE BELT 1232MM L	1232
1739979	SPA SECTION WRAPPED WEDGE BELT 1332MM L	1332
1739980	SPA SECTION WRAPPED WEDGE BELT 1432MM L	1432
1739981	SPA SECTION WRAPPED WEDGE BELT 1557MM L	1557
1739982	SPA SECTION WRAPPED WEDGE BELT 1782MM L	1782
1739983	SPA SECTION WRAPPED WEDGE BELT 1957MM L	1957
1739984	SPA SECTION WRAPPED WEDGE BELT 2182MM L	2182
1739985	SPA SECTION WRAPPED WEDGE BELT 2232MM L	2232
1739986	SPA SECTION WRAPPED WEDGE BELT 2300MM L	2300
1739987	SPA SECTION WRAPPED WEDGE BELT 2332MM L	2332
1739988	SPA SECTION WRAPPED WEDGE BELT 2432MM L	2432

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories