

RACON, square plunger 14 mm, L 7.6 mm



fields of application

- Measurement-control-regulation
- Mechanical and system engineering
- Automotive
- Signalling systems
- Vehicle construction
- Handheld terminals

description

The wide selection of standard plungers in different shapes and colors guarantees a versatile range of applications for the RACON tactile switch.

technical data

➤ general


Color	white
Collar shape	square
illuminated	No
Packaging unit	500 pcs.
net weight	0.4 g
MOQ order	1,000 pcs.
RoHS compliant	Yes
REACH compliant	Yes
Component material	Plastic

direct links

- [RAFI eCatalog](#)

➤ mounting diameters

Outside dimension, length	11.45 mm
Outside dimension, width	14 mm
Outside dimension, height	14 mm
Plunger length L	7.6 mm
Support height A	4.9 mm
Total height GH	12.5 mm

drawings**Dimensioned drawing****System drawing**