

## FEATURES

- Quick and easy to install
- 2m length
- Ideal for clean cable management.
- Open slotted
- Breakpoints on bars and channel floor

## RS PRO Grey Slotted Panel Trunking - Open Slot, W30 mm x D60mm, L2m, PVC

RS Stock No.: 136-9107



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

From the great value brand RS PRO, comes a range of high quality grey slotted cable trunking. Manufactured out of lead-free and flame retardant PVC this rigid trunking has been designed to allow the user to fix it to the area it will be applied to, allowing for a simple yet effective installation and secure cable organisation

## General Specifications

<b>Trunking/Chain Type</b>	Slotted Panel Trunking
<b>Material</b>	PVC
<b>Colour</b>	Grey
<b>Fire Behaviour</b>	Self-extinguishing
<b>UV Resistance</b>	PVC is conditionally permanent to UV- light, changes in colour under UV light cannot be excluded
<b>Angle</b>	90°
<b>Applications</b>	Electrical workshops, Offices and indoor work spaces, Schools, Hospitals and Hotels

## Mechanical Specifications

<b>Length</b>	2m
<b>Width</b>	30mm
<b>Depth</b>	60mm
<b>Slot Type</b>	Open
<b>Dielectric Strength</b>	>30kV/mm

## Operation Environment Specifications

Operating Temperature Range	-20°C to 60°C
-----------------------------	---------------

## Approvals

Standards Met	CE, CULus Recognised, DIN EN50085, EN45545 HL2, GL, VDE 0472
---------------	--

F2000	Height (H) in mm	Width (W) in mm							
	30	30							
40	25	30	40	60					
60	25	30	40	60	80	100	120	200*	
80	25	30	40	60	80	100	120		
100	30	40	60	80	100			150	
120		40	60	80					

\* Dimension 200x60 mm with a different punch picture

