



### Main

Range	Merten
Range compatibility	PlusLink
Product or component type	Presence detector
Device presentation	Complete product
Colour tint	Polar white (RAL 9010)

### Complementary

Device application	Lighting
Technology type	Electronic
Device mounting	Ceiling
Fixing mode	By screws and claws
Material	Thermoplastic
Surface finish	Glossy
Contacts type and composition	1 NO
[Ue] rated operational voltage	220/230 V
Network type	AC
Network frequency	50/60 Hz
Rated current	10 AX
Presence detection area	7 m radius
Detection angle	360°
Light intensity adjustment	10...1000 lux
Time delay range	10 s...30 min
Mounting height	2.5 m
IP degree of protection	IP20

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins