



Main

Range	MasterPacT
Range of product	MasterPact NT ComPact NS630b...1600 new generation
Device short name	MN
Product or component type	Voltage release
Device application	Control
Voltage release type	Opening coil Undervoltage release
Control type	Standard
[Uc] control circuit voltage	48 V AC 50/60 Hz 48...60 V DC
Circuit breaker mounting mode	Drawout
Range compatibility	Masterpact MasterPact NT ComPact ComPact NS630b...1600

Complementary

Operating threshold	0.35...0.7 x Un opening 0.85 x Un closing
Response time	40 ms +/- 5 % for MasterPact NT 90 ms +/- 5 % for Compact NS630b...1600
Supply holding power	4.5 VA

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
Sustainable packaging	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.