



3D Step-file
available on request



Further specifications and options in section „E-G“ / Weitere Spezifikationen und Optionen in Kapitel „E-G“ / Autres spécifications et options au chapitre „E-G“					
Type / Typ / Type	Voltage Spannung Tension	Body Körper Corps	Terminals Anschlüsse Raccords	Colour Farbe Couleurs	
962 	B 12 VDC	S silver anodized aluminium casing silber eloxiertes Aluminiumgehäuse argent anodisé boîtier en alu	F Faston 2,8 x 0,8 mm K cable 1,2 meters long Kabel 1,2 m lang cable 1,2 metre long	Y Yellow Gelb Jaune	
	D 24 VDC			B black anodized aluminium casing schwarz eloxiertes Aluminiumgehäuse noir anodisé boîtier en alu	B Blue Blau Bleue G Green Grün Verte R Red Rot Rouge W White Weiss Blanche
963 	X 115 VAC				
	Z 230 VAC				

Sloan_01_GK_Indicator-Lights_148

Operating Temperature -25° to +60°C / Storage Temperature: -25° to +60°C

RoHS compliant

Specifications are subject to change without notice – Änderungen die dem technischen Fortschritt dienen, sind vorbehalten – Réserve de modifications de toutes les données techniques

