

93RK/110 ROCK STEEL MONOBLOC

A CEN6, LPCB SR3 approved High Security Padlock for securing the most valuable of sites and assets



SECURITY LEVEL



CERTIFICATIONS



CEN GRADE



TEST SEALS



The ABUS 93RK is a CEN6 padlock and is built to secure assets of the greatest value. It has a shackle and lock body manufactured from hardened special steel with a patented Nano Protect™ coating that makes it highly resistant to harsh conditions.

This padlock is designed to protect high security sites, assets and goods, largely in the critical national infrastructure markets.

The design of this padlock is suited to high security perimeter gates and fencing.

The padlock is supplied to the end-user with an ABUS patented, registered, high security cylinder and key system.

TECHNOLOGY AND FEATURES

- EN12320 CEN Grade 6
- Lock body and shackle made of hardened special steel
- Hardened special steel shackle with NANO PROTECT™ coating for very high corrosion protection
- Cylinder protected against drilling, bumping, pulling open
- Double bolted locking mechanism increases the security of the lock
- Cylinder protection cap against moisture and dust optionally available
- Shackle Type: Sliding Bolt

Width	110 mm
Height	70 mm
Thickness	29 mm
Shackle Diameter	15 mm
Vertical shackle clearance	21.5 mm
Horizontal shackle clearance	34.5 mm