

BALL VALVES

RSIM - Parallel brass lever ball male-female valves PN 40



Part number	Material	Male thread	Female thread	Temperature min/max (°C)	Max. operating pressure	Net weight (Kg)	Dim. A (mm)	Dim. B (mm)
RSIMF 21	Brass	G1/2	G1/2	-10.00 / 80.00	40.00	0,26	50.00	25.00

