

Mounting Plate, PrismaSeT P, for Transfer Pact, 63A, 3P/4P, vertical fixed, W650

LVS03424

EAN Code: 3606482169951

Main

Range	TransferPacT	
Range of product	PrismaSeT P	
Device short name	TP	
Product or component type	Mounting plate	
Accessory / separate part category	Installation accessory	
Range compatibility	PrismaSeT P TP mounting plate	
installation description	Cubicle - width 650 + 150 mm depth 400 mm Cubicle - width 650 mm	
Enclosure mounting	Surface	
Mounting location	Top and bottom front of enclosure	
Mounting plate description	Dedicated	
Type of rail	Modular	
Installed device	Fixed with earth leakage protection - vertical installation	
Poles description	1 x 2P or 3P or 4P: panel mounting terminal blocks vertical installation	
Condition of using cable tie	-20-70 °C (6M high) when installation of device is in vertical	
Number of vertical modules [50 mm]	6 module(s): terminal blocks integrated earth leakage protection , direct in 650 + 150 mm Wide2 floor-standing enclosure (cable coming from top and bottom of enclosure) 6 module(s): terminal blocks integrated earth leakage protection , direct in 650 mm Wide2 floor-standing enclosure + duct (cable coming from top and bottom of enclosure)	
Standards	IEC 61439-2	
Product certifications	IEC	

Complementary

Connections - terminals	4 screw terminals terminal blocks switch	
Cable entry	Top and bottom 1.535 mm in front of support frame	
Material	On mounting holes: stainless steel	
Protective treatment	None	
Width	570 mm	
Height	197 mm	
Depth	16 mm	
Net weight	1.2 kg	
Quantity per set	1 kit	

Environment

IP degree of protection	> IP31 050 °C conforming to IEC 61439-2	
IK degree of protection	IK10 conforming to IEC 60947	
Mechanical robustness	IK protection 2555 °C, RH 95 % 2055 °C conforming to IEC 61439-2	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.000 cm
Package 1 Width	20.000 cm
Package 1 Length	58.000 cm
Package 1 Weight	2.420 kg
Unit Type of Package 2	P06
Number of Units in Package 2	15
Package 2 Height	34.500 cm
Package 2 Width	80.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	43.500 kg

Logistical informations

Country of origin Sk

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration
Halogen content performance	Halogen free product
PVC free	Yes

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No