

Model No. 411RED

Red Zenex™ Thermoplastic Safety Padlock, 1-1/2in (38mm) Wide with 1-1/2in (38mm) Tall Shackle

Best Used For:



Lockout Tagout



Multilingual Workforce



Safety Lockout/Tagout

Overview & Features

Product Features


- Thermoplastic Safety Padlock
- 1-1/2in (38mm) wide 3in (76mm) tall Thermoplastic red body, shackle with 1-1/2in (38mm) clearance
- Designed exclusively for lockout tagout applications
- Durable, lightweight, non-conductive Thermoplastic lock body
- Customize on-site with permanent, write-on labels
- Compliance with "One Employee, One Lock, One Key" directive
- High security, reserved-for-safety cylinder
- Key retaining - ensures that padlock is not left unlocked
- Keyed different, 6-pin tumbler with over 40,000 available key changes cylinder, Shelf Pack Qty 6, Master Carton Qty 36

Product Details

The Master Lock No. 411RED Zenex™ Thermoplastic Safety padlock features a 1-1/2in (38mm) wide, 3in (75mm) tall thermoplastic red body and a 1-1/2in (38mm) tall metal shackle. Designed specifically for safety lockout/tagout applications, padlock is key retaining to ensure that padlock is not left unlocked and the high-security reserved for safety 6-pin tumbler cylinder complies with the "one employee, one lock, one key" directive. Write-on, multi-language padlock labels are included for on-site customization.

Product Specifications

Product Number	411RED
Body Width	38mm
Shackle Dimensions	A: 6 mm B: 38 mm C: 20 mm
Colour	Red
Description	Keyed Different, Commercial Boxed Packaging
Shelf Pack Qty	6
Master Carton Qty	36



Master Lock Europe S.A.S.
10 avenue de l'arche - Le Colisée Gardens, bâtiment A - 92 400 Courbevoie - La Défense - France
O:+33-1-41437200 | F:+33-1-41437204
www.masterlock.eu