



Multi Purpose Abrasion Protection Ergonomic Protection



Light Duty

Durable industrial gloves, offering 2x more grip and up to 20% greater abrasion protection*

- **Improved durability and grip:** HyFlex® gloves with FORTIX™ Abrasion Resistance Technology provide twice the grip and ensure compliance with ANSI/ISEA and EN abrasion resistance standards*
- **Advanced ergonomics:** ERGOFORM™ Ergonomic Design Technology ensures a fit shaped to natural hand contours
- **Elevated comfort:** HyFlex® 11-840 safety gloves' ZONZ™ Comfort Fit Technology relieves tension, for optimal comfort
- **Guaranteed skin-friendliness and cleanliness:** HyFlex® 11-840 PPE gloves benefit from Dermatest® certification and an impurity-extracting proprietary washing process
- **Reduced contaminants:** Silicone-free, they prevent contaminant transfer to metal before painting
- **Certified harm-free:** They are also Oeko-Tex®-approved, certifying them free of substances harmful to human health Test



Industries

- Aerospace
- Automotive
- Machinery and Equipment
- Metal fabrication
- Automotive Aftermarket
- Emergency Medical Services
- Food Processing
- Oil and gas
- Utilities
- Warehousing

Applications

- Assembly of small parts
- General handling
- Raw material handling
- Picking, fastening components
- Adjusting systems and screwing
- Compatible with consumer and industrial touchscreens

Key Features

- **FORTIX™ Abrasion Resistance:** 2x more grip, up to 20% more durability*
- **ERGOFORM™ Ergonomic Design:** Reduced strain, better ergonomics
- **ZONZ™ Comfort Fit:** For safety gloves that offer breathable comfort

Technologies

 **ANSELL GRIP™**
Ansell Grip Technology

 **ERGOFORM™**
Ergonomic Design Technology

 **FORTIX™**
Abrasion Resistance Technology

 **Touchscreen Compatible**

 **ZONZ™**
Comfort Fit Technology

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-840	Finishing: Palm Coated Coating Material: Foam Nitrile Liner Material: Nylon, Spandex Cuff Style: Knitwrist	15	5, 6, 7, 8, 9, 10, 11, 12	200-275 mm/ 8-11 inches	Black	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.