

111E-HS

Adjustable wrenches with scales, chrome-plated, H-SAFE

DIN 3117 ISO 6787

- Right-hand rotation of pin
- Mm/inch scale

With H-SAFE tethered system



Features:

- Head angled at 15 degrees, allowing hardly accessible spaces to be reached
- New ergonomic properties resulting in 20% weight reduction
- Wide wrench opening
- Compact head with completely open jaw
- Right-hand rotation
- Double laser marking in mm/inches
- Matt chrome-plated heads for improved scale readout
- Matt chrome-plated body
- Made from high-performance alloy steel for increased mechanical torsional strength
- Special heat treatment for excellent wear resistance
- Large handle for optimized comfort
- Hole on handle for hanging wrench
- Complies with DIN 3117 - ISO 6787



Lightweight

Compact

Ergonomic

	art.				
001114120	111E-HS 200	200	8	29	265
001114125	111E-HS 250	250	10	34	387
001114130	111E-HS 300	300	12	40	685
001114138	111E-HS 380	380	15	45	1170
001114145	111E-HS 450	450	18	54	1780