



DIAMOND CORE MEDIUM MATERIAL: DRY

P-25622

Diameter: 117mm

DIAMOND CORE MEDIUM MATERIAL: DRY



TECHNICAL SPECIFICATIONS

Diameter (D)	117 mm
Overall Length	150 mm
Fitting	1/2" BSP
Pack Quantity	1

USER BENEFITS

- Top quality, European made, core, provides good cutting speed and long life. Minimal damage on break-out eliminates need to make good. Designed to cut medium brick, such as house brick and concrete blocks. The most popular range of dry diamond cores.
- Top quality, European made, core, provides good cutting speed and long life.. Minimal damage on break-out eliminates need to make good. Designed to cut medium brick, such as house brick and concrete blocks. The most popular range of dry diamond cores.
- Application: Brick, block, general purpose, plumbing, gas
- Application: Brick, block, general purpose, plumbing, gas
- Features: 7mm useable diamond. Slotted cores for easy core removal. 1/2
- Features: 7mm useable diamond. Slotted cores for easy core removal. 1/2
- Material: Most types of brick, concrete blocks.
- Star Rating: *****
- Material: Most types of brick, concrete blocks.

EAN 0088381952521

[Link to product - makitauk.com](https://makitauk.com)

