



Fuse-link, LV, 10 A, AC 240 V, BS88, 12 x 47 mm, gL/gG, BS

Catalog No. **STD10**

Similar to illustration

### Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			low voltage
Rated current	I	A	10
Rated voltage			AC 240 V
Construction size			BS88
Size			12 x 47 mm
Utilization category			gL/gG
Breaking Capacity		kA	33
usable for size/applications			street lighting cut-outs
Standard/Approval			BS
Shape			offset bolted tags (slotted)
Standards/Regulations			BS88-1

### Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			Other
Rated current		A	10
Rated voltage		V	240
Voltage type			AC
Rated switching capacity		kA	33
Utilization category			gL/gG (cable protection/equipment protection)
Type of fuse status indicator			None
Insulated metal gripping lugs (IMGL)			No

### Additional product information (links)

Product datasheet (pdf)	<a href="http://www1.cooperbusmann.com/pdf/1d499cae-a04f-4a72-9d4f-351f2614b0c2.pdf">http://www1.cooperbusmann.com/pdf/1d499cae-a04f-4a72-9d4f-351f2614b0c2.pdf</a>
-------------------------	---