



WX3 HOLSTER TROUSERS

DESCRIPTION

Contemporary work trouser featuring clever holster pockets for ample storage and security. Made from durable poly-cotton canvas fabric and includes triple stitched seams, these trousers have a multitude of practical features including two-tier knee pad pockets, a high rise back waistband and an adjustable leg hem for added convenience. Innovative stretch panelling provides excellent comfort and flexibility in key movement areas.

COMPOSITION

-  **Titanmill Plus Canvas: 65% Polyester, 35% Cotton Canvas Peach Finish, 245g**
-  **87% Nylon, 13% Elastane, 245g**
-  **Metal Grey 28-48**

FEATURES

- Durable soft polycotton canvas for high performance and maximum wearer comfort
- Innovative stretch panelling in key movement areas provides excellent comfort and flexibility
- Gripper elasticated inner waistline helping keep upper body garments in place
- Triple-stitched seams for extra durability
- Swing away tool pockets
- Two tier knee pad pockets allowing two positioning options
- 12 Pockets for ample storage
- 2 Side pockets
- Bottom loading knee pad pockets
- 1 Rule pocket
- 1 ID card holder
- 2 side zip pockets for secure storage

STANDARDS

EN 14404: 2004 + A1: 2010 Type 2 Level 0 (When used in combination with S156)

COLOUR / SIZES

SKU	COLOUR	SIZE RANGE
T702MGR	METAL GREY	28-14

FEATURES



STRETCH PANELS
Innovative stretch panelling in key movement areas provides excellent comfort and flexibility



BOTTOM LOADING KNEE PAD POCKETS
Knee pad pockets to facilitate knee pads



UPF 40+
40+ UPF rated fabric to block 98% of UV rays



TECHNICAL STRONG WORKWEAR
Technical Strong Workwear built with innovative fabrics that will make your work day more comfortable.

GET THE COLLECTION

TECHINCAL INFORMATION



· Wash garment inside out and fully fastened

Item	Colour Fit	Len (cm)	Wid (cm)	Hgt (cm)	Weight (Kg)	Cubic (m³)	EAN13	GTIN/DUN14
T702MGR28	Metal Grey	65	45	36	1.070	5850.000	5036108305308	15036108794406
T702MGR30	Metal Grey	65	45	36	1.080	5850.000	5036108305315	15036108794413
T702MGR32	Metal Grey	65	45	36	1.090	5850.000	5036108305322	15036108794420
T702MGR33	Metal Grey	65	45	36	1.100	5850.000	5036108305339	15036108794437
T702MGR34	Metal Grey	65	45	36	1.100	5850.000	5036108305346	15036108794444
T702MGR36	Metal Grey	65	45	36	1.120	5850.000	5036108305353	15036108794451
T702MGR38	Metal Grey	65	45	36	1.140	5850.000	5036108305360	15036108794468
T702MGR40	Metal Grey	65	45	36	1.160	5850.000	5036108305377	15036108794475
T702MGR41	Metal Grey	65	45	36	1.170	5850.000	5036108305384	15036108794482
T702MGR42	Metal Grey	65	45	36	1.190	5850.000	5036108305391	15036108794499
T702MGR44	Metal Grey	65	45	36	1.210	5850.000	5036108305407	15036108794505
T702MGR46	Metal Grey	65	45	36	1.230	5850.000	5036108305414	15036108794512
T702MGR48	Metal Grey	65	45	36	1.235	5850.000	5036108305421	15036108794529