



ENGLISH

Datasheet

Stock No: 235-764

RS Pro Incandescent Beacon, Flashing, Surface Mount, 12 V dc



Product Details

Flashing Filament Beacons

Standard flashing filament beacons for use in all applications

When used with an amber lens, beacon is approved to CAP168 for airport use

Single voltage units with bulb included

IP56 protection

153mm diameter

Flash rate: 75 fpm

Operating temperature range: -30 to +50°C

Magnetic versions rated to 70mph

Note

Lens must be purchased separately

Approvals

EMC, ECE65, CAP168

Supplied with

Bulb



ENGLISH

Specifications:

Supply Voltage	12 V dc
Light Effect	Flashing
Lens Colour	Lens Not Included
Mounting Style	Surface Mount
Bulb Type	Incandescent
Current Type	DC
Base Diameter	153mm
Housing Colour	Black
Lamp Included	Yes
Series	V10996
Height	175mm
Maximum Temperature	+50°C
Minimum Temperature	-30°C