

## FEATURES

- **Flexible design:** Easily adapts to different surfaces and shapes for versatile installation
- **IP54 rating:** Provides protection against dust and water splashes, suitable for indoor and semi-outdoor use
- **60 LEDs per metre:** Ensures consistent and bright illumination across the strip
- **4.8 W/m power consumption:** Energy-efficient operation reduces electricity costs
- **8 mm strip width:** Compact design allows for discreet installation in tight spaces
- **CE and RoHS compliant:** Meets key safety and environmental standards

## RS PRO Flexible LED Strip Light, 5m Length

RS Stock No: 558-395



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO flexible LED strip light is designed for versatile lighting solutions, offering a bright and efficient illumination with a colour temperature range of 6000 to 6500 K. Ideal for both commercial and residential applications, it provides a luminous flux of 415 lm/m, ensuring optimal brightness. The strip is 5 metres long and operates at 24 V DC, making it suitable for various installations.

## General Specifications

Colour Temperature	6000-6500 K
Flexible/Rigid	Flexible
LED Colour	White
LED Pitch	16.6 mm
Number of LEDs Per Metre	60
Product Type	LED Strip Light
Typical Luminous Flux (lm/m)	415 lm/m

## Protection Category

IP Rating	IP54
-----------	------

## Electrical Specifications

Power Per Metre	4.8 W/m
Voltage	24 V dc

## Approvals

Standards/Approvals	CE, RoHS
---------------------	----------

## Mechanical Specifications

Strip Length	5 m
Strip Width	8 mm

