

Profile mounting
EAHF-V2-80/100-P
Part number: 1547780

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper, zinc or nickel by mass are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Element installed statically, no meaningful evaluation possible according to ISO 14644-1
Max. axial force	1600 N
Product weight	570 g
Note on materials	RoHS-compliant