Prism Pro XM

Part of the Downlights product category

Model	Prism Pro XM Fire Rated Downlight
Code	APRIPXM/1
Application	Residential

GENERAL INFORMATION

Input	220-240V
Wattage	5W/7W
Operating Temp	-10°C - 35°C
Lumens Delivered	640lm - 820lm (4000K)
lm/W	135lm/W
CCT	2700K/3000K/4000K/6000K
UGR	28
Beam Angle	60

MATERIAL INFORMATION

Main Material	Polycarbonate, Steel
Product Weight without Packaging	0.27 kg
Colour / Finish	White
Diameter	88 mm
Height	63 mm

TECHNICAL INFORMATION

Class Protection	2
Light Source	LED
SDCM (Initial Macadam)	5
CRI	80
Internal / External	Internal
Surface / Recessed / Suspended	Recessed
Power Factor	0.95
L70 @ 25°C	L70 60,000h

PRODUCT FEATURES

- IP65 dimmable LED Fire Rated Downlight suitable for residential and hospitality applications
- TM66 2.5 assessed – independently evaluated against the industry standard for measuring the circularity of lighting products.
- CCT selectable between 2700K, 3000K, 4000K and 6000K and power selectable; offering a choice of 2 outputs, in one luminaire
- Innovative 2 part detachable connector design allows initial wiring and testing to be completed first, then simply plug the downlight back to the connector, ensuring a quick and simple installation
- Patent-approved modular design with replaceable light engine and driver — extend product life and reduce waste through easy part replacement.

ACCESSORIES

APRIPXM/LE/1	Prism Pro XM Replacement Light Engine
APRIPXM/DRI/1	Prism Pro XM Universal Replacement Driver
APRIPXMBZ/BK	Prism Pro XM Bezel - Matt Black
APRIPXMBZ/SC	Prism Pro XM Bezel - Satin Chrome
APRIPXMBZ/CH	Prism Pro XM Bezel - Chrome
APRIPXMBZ/AB	Prism Pro XM Bezel - Antique Brass
APRIPXM/CP/BK	Prism Pro XM Converter Kit - Matt Black
APRIPXM/CP/SC	Prism Pro XM Converter Kit - Satin Chrome
APRIPXM/CP/CH	Prism Pro XM Converter Kit - Chrome
APRIPXM/CP/AB	Prism Pro XM Converter Kit - Antique Brass

Prism Pro XM

Part of the Downlights product category

Model	Prism Pro XM Fire Rated Downlight
Code	APRIPXM/1
Application	Residential