



Part Number : [1210503398](#)
Product Description : mPm DIN Valve Connector, Form C - 8mm, 2 Pole Plus Ground, to 5.0m (16.40') PUR UL Cable Pigtail, Yellow LED, Black Nitrile Gasket, 115V
Series Number : 121050
Status : Obsolete
Product Category : Circular Industrial Cordsets
Engineering Number : E492B2A50011S0L



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Obsolete
Category	Circular Industrial Cordsets
Series	121050
Description	mPm DIN Valve Connector, Form C - 8mm, 2 Pole Plus Ground, to 5.0m (16.40') PUR UL Cable Pigtail, Yellow LED, Black Nitrile Gasket, 115V
IP Rating	IP65
Product Name	mPm
Protocol	N/A
Type	Single Ended
UPC	78172534610

Electrical

Current - Maximum per Contact	N/A
Voltage - Maximum	115V

Physical

Cable Diameter	5.72mm (.225")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Connector End A	Brad mPm DIN C - 8mm
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	None
LED Indicator	Yellow
Material - Cable Jacket	PUR UL
Material - Connector Body	Polypropylene
Material - Contact	Brass
Material - Coupling Nut	N/A
Material - Plating Mating	Gold
Orientation	90° to Pigtail
Poles	2

Temperature Range - Operating	-40° to +90°C
Wire/Cable Type	N/A
Wire Size (AWG)	20