



Part Number : 1301110023
Product Description : Pro-Yellow Stringlight, 150W, 14/2 AWM with 2.43m Lead, 10 Sockets with Guards, Overall Length 30.48m (100.0')
Series Number : 130111
Status : Active
Product Category : Lamps and Lights
Engineering Number : 202SRL



Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
--------	--------

Category	Lamps and Lights
Series	130111
Description	Pro-Yellow Stringlight, 150W, 14/2 AWM with 2.43m Lead, 10 Sockets with Guards, Overall Length 30.48m (100.0')
NEMA Configuration	N/A
NEMA Rating	Rain Tight
Product Name	Pro-Yellow
Type	String Lights
UPC	78678853637

Electrical

Lamp Wattage - Maximum	150W
Lumens	1500
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Physical

Bulb Type	Incandescent
Cord Length - Primary	2.43m (8.0')
Cord Length - Secondary	0.61m (2.0')
Cord Type - Primary	14/2
Depth	N/A
Duty	General
Guard Included	Yes
Guard Type	Polypropylene
Height	N/A
Lamp Type	A21
Length	30.48m (100.0')
Material - Guard	Polypropylene
Mounting Style	Stringer
Net Weight	4.105/kg
Outlet	None
Packaging Type	Carton
Socket Construction	Assembled

This document was generated on Mar 27, 2025