

Features

- *Conductor*
Material: tinsel wires
- *Jacket Material:*
PVC, black
- *Cable Length:* 5M
- *Easy to install and reliable connection*
- *Color:* Black

RS PRO Telephone Cable

RS Stock No.: 0707870



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against

demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

This is a coiled RJ10 4P4C to RJ10 4P4C data cable for both data and voice use, coiled length is 600mm, extended length is 5M. It is good for long-distance communication for your desk phone or office phone. Extended length coiled cord is provided extra length for working in the office or at home. Both ends are durable RJ10 4P4C modular connector. Straight-through pin out for both data and voice use.

Can be used as phone handset or receiver extension cable, data cable, controller cable, digital motor cable, mic cable etc. It is compatible with landline telephones such as: AT&T / Cisco / NEC / Rolm / ITT / Ti ect.

General Specifications

Number of Strands	4
Conductor Strand Type	Stranded
Terminated/Unterminated	Terminated; Unterminated
Connector Type	Male RJ10/RJ10
Connector B	Male RJ10
Connector A	Male RJ10
Outer Sheath Material	PVC;
Sheath Colour	Black
Conductor Material	Tinsel Copper wire
Drain Wire	No
Fire Behaviour	Flame Retardant.

Mechanical Specifications

Length	5m
Outer Diameter	5.0*2.5mm
Sheath Thickness	0.6mm

<i>Insulator Diameter</i>	0.9mm +/-0.05
<i>American Wire Gauge</i>	28AWG
<i>Cross Sectional Area</i>	0.079mm ²
<i>Size of Strands</i>	7/0.12mm, 28AWG
<i>Core Strands</i>	7/0.12mm

Approvals

<i>Compliance/Certifications</i>	RoHS, Reach
<i>Declarations</i>	RoHS, Reach

