


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



# **SPECIFICATIONS:**

PANDUIT TOOL NO.: STHV  
TOOL WEIGHT: 13 oz. (367 gr.)

INSTALLS LIGHT-HEAVY AND HEAVY  
CROSS SECTION CABLE TIES.

CABLE TIE CROSS-SECTION CODE:  
LH = LIGHT-HEAVY  
H = HEAVY

THIS TOOL TIGHTENS CABLE TIE AFTER  
INSTALLING TIE AROUND BUNDLE; THE  
HANDLES ARE SQUEEZED TO PROVIDE  
TENSION. A SEPARATE LEVER CUTS  
EXCESS TIE.

DIMENSIONS SHOWN IN PARENTHESES  
ARE METRIC.

DIMENSIONS ARE FOR REFERENCE ONLY.

## **\*\* TIE WINDOW DIMENSIONS**

|        | MIN         | MAX         |
|--------|-------------|-------------|
| HEIGHT | .094 (2.39) | .108 (2.74) |
| WIDTH  | .369 (9.37) | .383 (9.73) |

F:\wrkgrp\rvusers\ENGR DOCS-NEW\CUSTOMER DRAWINGS\WE24515A01\_05 STHV CD.doc

|     |          |     |       |                                |      |    |      |     |                                                                                                                                                             |                                                                                                  |                   |                  |
|-----|----------|-----|-------|--------------------------------|------|----|------|-----|-------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------|-------------------|------------------|
|     |          |     |       |                                |      |    |      |     | <div>PANDUIT CORP. TINLEY PARK, ILLINOIS</div> <div>STHV CUSTOMER DRAWING</div>                                                                             |                                                                                                  |                   |                  |
| 05  | 1-16-12  | BLR | ABJ   | UPD LOGO; TOOL GRAPHIC         | 4422 | -- | LAH  |     | UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE:<br><br>(.x) ± —                      (.xxx) ± —<br><br>(.xx) ± —                      ANGLES ± — | UNLESS OTHERWISE SPECIFIED,<br>ALL DIMENSIONS ARE GIVEN IN<br>INCHES, THIRD ANGLE<br>PROJECTION. |                   |                  |
| 04  | 10-13-06 | BLR | ABJ   | UPD LABEL-TAIWAN               | 4200 | -- | LAH  |     |                                                                                                                                                             |                                                                                                  |                   |                  |
| 03  | 5-26-06  | BLR | ABJ   | UPD LABEL DESIGN               | 4200 | -- | LAH  |     |                                                                                                                                                             |                                                                                                  |                   |                  |
| 02  | 11-12-04 | BLR | MBR   | UPDATE LABEL                   | 4147 | -- | DLWE |     | DRAWN BY:<br>BLR                                                                                                                                            | MATL:<br><br>CUSTOMER<br>DRAWING                                                                 | SCALE<br><br>NONE |                  |
| 01  | 3-02-04  | BLR | ABJ   | REDRAWN; CHNG<br>WEIGHT TO OZ. | 4121 | -- | DLWE |     | DATE:<br>3-02-04                                                                                                                                            |                                                                                                  | DRAWING NO.       | DWG<br>A<br>SIZE |
| REV | DATE     | BY  | CHK'D | DESCRIPTION                    | ECN  | -R | CUST | SUP | CHK'D:<br>ABJ                                                                                                                                               |                                                                                                  | WE24515A01        |                  |