



tesa[®] PRO 66462

Product Information

Professional strong Repairing tape for long-lasting bonds

Product Description

For professional craftsmen who demand top-quality tools, the tesa PRO STRONG Duct Tape 66462 is the ultimate choice. This versatile and reliable repairing tape boasts extra strong bonding power, making it perfect for a wide range of applications. With its easy tearability and flexibility, this duct tape provides invaluable support for quick solutions throughout your busy workday.

Not only is it highly functional, but the tesa PRO STRONG Duct Tape 66462 is also designed to withstand various conditions. It repels water and offers short-term resistance to high temperatures, making it suitable for both indoor and outdoor use. The tape consists of a polyethylene film and a woven polyester fabric backing, which is made from over 60% post-consumer recycled materials. Additionally, it features a synthetic rubber adhesive for optimal adhesion. Available in different dimensions, you can choose the size that best fits your specific needs.

Product Features

- tesa PRO STRONG Duct Tape for professionals of every craft, your general purpose tape that is easy to apply and works even on slightly rough surfaces.
- PRO STRONG Duct Tape is truly reliable for various applications like sealing, repairing, fastening or packaging.
- Backing made from more than 60% post-consumer recycled materials - increasing sustainability and reducing waste!
- Based on synthetic rubber, this new PRO STRONG Duct Tape has never been stronger while still being easy to unwind and convenient to tear. Use indoors or outdoors.
- A must-have for every craftsmen toolbox: The tesa PRO STRONG Duct Tape is for temporary and permanent applications, the perfect all round support with superior tesa quality.

Application Fields

This Duct Tape works best on clean, smooth surfaces. Apply the tape and press firmly onto the surface.

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

- | | | | |
|---|--------------------|--------------------|------------------|
| • Backing material | PE laminated cloth | • Type of adhesive | synthetic rubber |
| • Bio-based carbon content of liner (acc. DIN EN 16640) | 67 % | • Total thickness | 230 µm |

For latest information on this product please visit <http://l.tesa.com/?mp=66462>



tesa[®] PRO 66462

Product Information

Properties/Performance Values

• Elongation at break	16 %	• Hand tearability	good
• Tensile strength	41.2 N/cm	• Humidity resistance	yes
• Abrasion resistance	very good	• Residue free removal	no
• Adhesive strength	High adhesion	• Solvent free	yes
• Ageing resistance (UV)	yes	• Tear resistance	yes
• Chemical resistance	yes	• Writable	yes

Disclaimer

tesa[®] products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa[®] product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.

For latest information on this product please visit <http://l.tesa.com/?mp=66462>