



|                                   |                                   |
|-----------------------------------|-----------------------------------|
| <b>Product-Nr.</b>                | 156410-11                         |
| <b>EAN:</b>                       | 4260556627427                     |
| <b>Model:</b>                     | TUBELED_70 EVO AC                 |
| Order number:                     | 156410-11                         |
| <b>Model:</b>                     | TUBELED_70 EVO AC                 |
| <b>Illuminant:</b>                | SMD LED                           |
| <b>Total output incl. driver:</b> | 54 W                              |
| <b>Power consumption:</b>         | 49 W                              |
| <b>Lamp luminous flux:</b>        | 7596 lm                           |
| <b>Lamp luminous efficiency:</b>  | 155 lm/W                          |
| <b>Light colour:</b>              | 5600K 3-step MacAdam              |
| <b>Number of poles:</b>           | 3                                 |
| <b>Connected load:</b>            | 120-277V AC, 50 - 60 Hz           |
| <b>Power supply:</b>              | integrated                        |
| <b>Connection (connector):</b>    | M12 S-coded                       |
| <b>Degree of protection:</b>      | IP67/IP69K                        |
| <b>Class of protection:</b>       | I                                 |
| <b>Glare control:</b>             | diffuser film                     |
| <b>Beam angle (optics):</b>       | 100°                              |
| <b>Operating temperature:</b>     | -20 °C - +60 °C (-4 °F - 140 °F)  |
| <b>Storage temperature:</b>       | -20 °C - +80 °C (-4 °F - 176 °F)  |
| <b>Colour rendering (Ra):</b>     | >85                               |
| <b>Lamps lifetime:</b>            | > 100,000 h (L80/B10)             |
| <b>Housing material:</b>          | Aluminum, glass                   |
| <b>Height [B] x Width [C]:</b>    | 59,5 mm x 70 mm (~2,34" x ~2,76") |
| <b>Length [A]:</b>                | 1100 mm (~43,31")                 |
| <b>Weight (net):</b>              | 3150 g (~111 oz)                  |
| <b>Gross weight:</b>              | 3930 g (~139 oz)                  |
| <b>Risk group (DIN EN 62471):</b> | free group                        |
| <b>Markings:</b>                  | CE, UKCA, ETL Listed (5003529)    |
| <b>Dimmable:</b>                  | no                                |
| <b>Mounting accessories:</b>      | optional                          |
| <b>Made in:</b>                   | Germany                           |