



WT 1014

Item No: T0053442699N

1-Channel Soldering Station Set, 95 W
with soldering iron WSP 80 Robust

KEY FEATURES

- + Power unit WT 1, 1 channel with soldering iron WSP 80 Robust and safety rest WSR 201
- + WSP 80 Robust soldering iron (80 W) with power response tips for all standard applications, robust version. Tip family LT
- + High productivity (Power unit with 1 channel, 95 W)
- + Intuitive use thanks to clear menu structure
- + Reduced footprint thanks to stackability
- + Graphical backlit LC-Display
- + High performance and functionality - many connectable tools
- + Housing cover useable as storage
- + OFF time, Process window, Lock function, Offset

TECHNICAL DATA

Height	101mm
Length	149mm
Dimensions L x W x H	149.0 x 138.0 x 101.0mm
Equipotential Bonding	Yes
Equipotential Bonding Socket	Via 3.5mm Pawl Socket on Front of Device
ESD Safe	Yes
Fuse	0,5A
Interface	One Switching Output
Number of Channels	1
Power	95 W
Temperature Accuracy °C	± 9 °C
Temperature Accuracy °F	±17 °F
Temperature Range (Depends on Tool)	Adjustable from 50°C - 450°C (150°F - 850°F) Adjustable temperature range varies among tools
Temperature Range °C	50 - 450 °C
Temperature Range °F	150 - 850 °F
Temperature Stability °C	±2 °C
Temperature Stability °F	±4 °F
UPC	4003019438464
Voltage	230 V, 50/60 Hz
Weight (Catalog)	1.90 kg