

A.MTJ1 - MICRO-TECH® TORQUE SCREWDRIVER SETS | A.301MTJ1



Norm :

NF EN ISO 6789, ISO 6789, DIN EN ISO 6789

Description

- Lightweight and compact screwdriver for low torque load.
- Right-hand torquing.
- Female hex output for use with bits series 0 - 4 mm (1/4" output with ECR.O drive optionally).
- Bits series 0 drive 4 mm.
- Adjustment key 4 mm.
- Supplied in case with calibration certificate.

Information

Capacity [cN.m]	15 - 75
Bits	Slotted head: 4 - 4,5 - 5,5, PH 1,5 - 2,5 - 3 mm, PZ 0 - 1 mm
Screwdriver	A.301MT
[g]	370