

Pipe Wrenches



Part No.	O/A Length		Max Jaw Opening		Weight(Kg)	Performance Under Standard Torque	
	mm	inches	mm	inches			
422-2686	87-621	186	8	34	1.33	0.38	373N.M
422-2715	87-623	297	12	55	2.16	1.14	1129N.M
422-2721	87-624	332	14	65	2.55	1.4	1468N.M
422-2737	87-625	414	18	80	3.14	2.38	2258N.M
422-2743	87-626	553	24	95	3.74	3.83	3161N.M