

FEATURES

- **Heat Stabilised Material:** Ensures performance in high-temperature environments up to 105 °C
- **UL 94 V-2 Fire Behaviour:** Provides a level of flame retardancy for added safety
- **Tensile Strength of 8 kg:** Offers robust holding power for secure bundling
- **Maximum Bundle Diameter of 55 mm:** Accommodates a wide range of cable sizes
- **Light Green Colour:** Allows for easy identification and organisation

RS PRO 203 mm Nylon Cable Tie, Heat Stabilised

RS Stock No: 656-018



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These RS PRO cable ties are designed for securing and organising cables efficiently. Made from durable nylon, they are ideal for use in environments requiring heat stability. The main benefit is their ability to withstand high temperatures, making them suitable for various industrial applications.

General Specifications

Colour	Light Green
Product Type	Cable Tie
Sub Type	Heat Stabilised
Tensile Strength	8 kg

Protection Category

Fire Behaviour	UL 94 V-2
UV Resistant	No

Mechanical Specifications

Length	203 mm
Material	Nylon
Maximum Bundle Diameter	55 mm
Width	2.5 mm

Operation Environment Specifications

Maximum Operating Temperature	105 °C
-------------------------------	--------

Approvals

Standards/Approvals	ABS 15-TA1338482-PDA, cULus E97527, RoHS, UL94V-2
---------------------	---