

5

4

3

2

1

D



Description: CAT5E assembled patch cable  
 Part No: 73-777X-XXX  
 Application: Patch cable  
 Crimp Tool: N/A  
 Impedance: N/A  
 Frequency Range: N/A  
 Material: Plug RJ-45, Gold plated on contacts  
 Cable UTP, 24 AWG, 4 twisted pairs, stranded bare copper, UL ETL EIA/TIA-568B verified category 5e

DRAWING NO. 73-777X-XXX-CUST	
<b>REVISIONS</b>	
OFFICIAL RELEASE	
01	03-28-11 J J D  03/28/11 09:59:14 -09'00'

D

C

RoHS Compliance: Yes  
 Technical Detail: N/A

C


PIN ASSIGNMENT		
	P1	P2
WHITE/ORANGE	1	1
ORANGE	2	2
WHITE/GREEN	3	3
GREEN	6	6
BLUE	4	4
WHITE/BLUE	5	5
WHITE/BROWN	7	7
BROWN	8	8

X=COLOR  
 0-GRAY  
 1-BLACK  
 2-BLUE  
 3-GREEN  
 4-RED  
 5-YELLOW  
 6-WHITE  
 7-ORANGE  
 8-PINK  
 9-PURPLE

TABLE 1

PART NUMBER	LENGTH (FEET)	DESCRIPTION
73-777X-1	1	CAT5E ASSEMBLED PATCH CABLE, 1FT
73-777X-3	3	CAT5E ASSEMBLED PATCH CABLE, 3FT
73-777X-5	5	CAT5E ASSEMBLED PATCH CABLE, 5FT
73-777X-7	7	CAT5E ASSEMBLED PATCH CABLE, 7FT
73-777X-10	10	CAT5E ASSEMBLED PATCH CABLE, 10FT
73-777X-14	14	CAT5E ASSEMBLED PATCH CABLE, 14FT
73-777X-25	25	CAT5E ASSEMBLED PATCH CABLE, 25FT
73-777X-50	50	CAT5E ASSEMBLED PATCH CABLE, 50FT
73-777X-100	100	CAT5E ASSEMBLED PATCH CABLE, 100FT

B



B

**CUSTOMER COPY**

A

A

**DIM OUTLINE**

受控 CONTROLLED DOCUMENT					
编号 P/N	73-777X-XXX-CUST	版本 Rev	01	日期 Rel'd Date	Jul11,11

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY	DATE
DECIMALS	mm	JEAN.JIN	03-28-11
X	± 0.5	CHECKED BY	DATE
X.X	± 0.3	JEAN.JIN	03-28-11
X.XX	±0.15	APPROVED BY	DATE
ANGLES	± 0.5°	DONALD	03-28-11
		U/M	mm



TITLE  
 CAT5E ASSEMBLED PATCH CABLE

SHEET 1 OF 1	DRAWING NO. 73-777X-XXX-CUST	SIZE A
-----------------	---------------------------------	-----------

THIS DRAWING WAS PRODUCED BY COMPUTER,  
 DO NOT SCALE DRAWING OR UPDATE MANUALLY.

5

4

3

2

1