




NOTES:

- 1 ATTENUATION $\leq 0,3$ dB, MEASURED AT 1300nm ACC. TO IEC 874-1
CLAUSE 4.4.7 METHOD 7 EQUILIBRIUM MODE CONDITION
- 2 INDIVIDUAL LENGTH DIFFERENCE ON BOTH SIDES ≤ 50 mm
- 3 SUPPLY FILLED OUT TEST RESULT SHEET WITH EACH
INDIVIDUALLY PACKED ASSEMBLY
- 4 DAT LABEL INFO:
- UNIQUE SERIAL NUMBER
- TYCO LOGO PN
- MANUFACTURING LOCN.
- 5 BLANK LABEL
- 6 CABLE INFO:
CORE DIA - 50/125 μ m
OUTER DIA - 2,5 x 5,0 mm
JACKET COLOR - ORANGE
JACKET MATERIAL - LSZH

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (Meter)
X-5349561-Y	XY,0
4-5349561-1	1,5
9-5349561-1	15,5

2	—	DAT-85 LABEL	7
4	—	PROTECTIVE COVER, 2.5MM, BLACK	6
4	—	KIT, MM, CER, ASSY, BULK	5
4	—	CRIMP EYELET, BRIGHT TIN	4
2	—	FOAC BOOT 2.5BAY,BLACK	3
2	—	FOAC BOOT 2.5BAY,RED	2
L	—	FOCAB 2.5 50/125 DUPLEX ORANGE	1
Qty	Part Number	Description	Item

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

MATERIAL

—

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH —

DWN 13 SEP 05 GIRIYAPPA. M

CHK 13 SEP 05 DIWAKAR BELAVADI

APVD 13 SEP 05 DIWAKAR BELAVADI

PRODUCT SPEC —

APPLICATION SPEC —

WEIGHT —

CUSTOMER DRAWING

tyco
Electronics

Tyco Electronics Corporation
FOBU, Bangalore, India

NAME

FOMM50 LEAD 2,5mm TZ ST - ST DPX

SIZE A2

CAGE CODE 00779

DRAWING NO C=5349561

RESTRICTED TO —

SCALE NTS

SHEET 1 OF 1

REV A