



PRODUCT-DETAILS

TY25MFR-RW

TY25MFR FOR RAILWAY



General Information

Extended Product Type	TY25MFR-RW
Product ID	7TCG009570R0010
EAN	5415022180374
Catalog Description	TY25MFR FOR RAILWAY
Long Description	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 185mm (7.3 Inches), Width of 4.6mm (0.18 Inch), Thickness of 1.3mm (0.05 Inch), Maximum Bundle Diameter 48mm (1.89 Inches), Tensile Strength Rating of 220 Newtons (49 Pounds)

Ordering

EAN	5415022180374
UPC	786209719164

Dimensions

Product Net Width	0.189 in 4.8 mm
Product Net Depth / Length	7.32 in 186 mm

Container Information

Package Level 1 Units	1000 piece
-----------------------	------------

Package Level 1 Width	10.21 in 259 mm
Package Level 1 Height	1.96 in 50 mm
Package Level 1 Depth / Length	14.14 in 359 mm
Package Level 2 Units	10000 piece
Package Level 2 Width	10.21 in 259 mm
Package Level 2 Height	14.14 in 359 mm
Package Level 2 Depth / Length	19.65 in 499 mm

Technical UL/CSA

Flammability According to UL94	V-0
--------------------------------	-----

Additional Information

Brand / Label	Ty-Rap
Color	White
Effective Date	20130731
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	OTHER ARTICLES OF PLASTIC

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TDS000478
Instructions and Manuals	TY25MFR-RW
REACH Declaration	9AKK107992A4002
RoHS Information	9AKK107991A8072

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

