1844 Automatic cable reel, with 3Gx1.5 mm² cable

CE IP42

Features:
- 3Gx1.5 mm² cable
- With thermal protection switch
- Cable length out of drum: 1 m (except for 1844 30-H05, 2 m)
- Supplied without incoming cable
- Rack mechanism can be disabled to keep cable pulled
- Max. power (rolled up): 1500W (230V-20°C)
- Max. power (unrolled): 2500W (230V-20°C)
- Supplied with a 180° swivel bracket and an additional quick connection bracket

	art.	Cavo	L m	Scocca	
018440310	1844 10-H05	H05VV-F	10+1	A	3,9 kg
018440315	1844 15-H05	H05VV-F	15+1	A	4,6 kg
018440317	1844 15-H07	H07RN-F	14+1	A	9,7 kg
018440330	1844 30-H05	H05VV-F	30+2	B	5,2 kg









