

Product Information



UOO080x34-Ø12

EAN 4031582070095

Wheel centre made of Polyamide, plain bearing

Technical Data

Wheel diameter	80 mm
Width of Tread	34 mm
Axle Hole-Ø	12 mm
Hub length	44.4 mm
Temperature	- 40 / + 80 °C
Standard	EN 12532
Weight	0.078 kg
Hardness of tread	Shore D 75
Load capacity	200 kg
Load capacity (static)	400 kg



Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+

