



3D Step-file available on request



955YY0B

**Further specifications and options in section „E-G“ / Weitere Spezifikationen und Optionen in Kapitel „E-G“ / Autres spécifications et options au chapitre „E-G“**

| Type / Typ / Type  | Body / Körper / Corps   |                                       | Accessories<br>Zubehör<br>Accessoires                    | Cap / Farbkappe /<br>Cabochon    | Light source<br>Lichtquelle<br>Source lum.                     | Voltage<br>Spannung<br>Tension |    |                       |
|--|---|---------------------------------------|--|----------------------------------|--|--------------------------------|----|-----------------------|
|  | Surface<br>Oberfläche<br>Surface  | Protection<br>Schutzart<br>Protection |  |                                  |  | Code                           | V  | mA                    |
| <b>955</b><br><br><br><br>All versions also available as flashing units. Put a "F" for flashing at the end of the part#.<br><br>Alle Versionen auch blinkend erhältlich. Bitte ergänzen Sie ein „F“ am Ende der Artikel#.<br><br>Version clignotante possible pour tous les modèles. Ajouter la lettre "F" à la référence. | Black<br>Schwarz<br>Noir<br><br>Material: ABS<br>Material: ABS<br>Matériel: ABS | IP65                                  | Nut & O-Ring<br>Mutter & O-Ring<br>Ecrou & Joint<br><br> | <b>B</b> Blue<br>Blau<br>Bleu    | <b>B0</b> 1 LED<br>3'000mcd<br>470nm Blue<br>Blau<br>Bleue     | <b>B</b> 12V<br>AC/DC          | 20 |                       |
|  |   |                                       |  | <b>G</b> Green<br>Grün<br>Vert   | <b>G0</b> 1 LED<br>3'000mcd<br>525nm Green<br>Grün<br>Verte    |                                |    | <b>D</b> 24V<br>AC/DC |
|  |   |                                       |  | <b>R</b> Red<br>Rot<br>Rouge     | <b>R0</b> 1 LED<br>800mcd<br>660nm Red<br>Rot<br>Rouge         |                                |    | <b>J</b> 48V<br>AC/DC |
|  |   |                                       |  | <b>W</b> White<br>Weiss<br>Blanc | <b>W0</b> 1 LED<br>1'000mcd<br>6500K White<br>Weiss<br>Blanche |                                |    |                       |
|  |   |                                       |  | <b>Y</b> Yellow<br>Gelb<br>Jaune | <b>Y0</b> 1 LED<br>800mcd<br>592nm Yellow<br>Gelb<br>Jaune     |                                |    |                       |

Operating Temperature -25° to +60°C / Storage Temperature: -25° to +60°C

RoHS compliant

Specifications are subject to change without notice – Änderungen die dem technischen Fortschritt dienen, sind vorbehalten – Réserve de modifications de toutes les données techniques

