




Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought






TE Part #6-1393292-3
V23074A2002A403-EV-CBOX




TE Part #823696-000
382A023-25-0



TE Part #CAT-R21-731072
Bulbous Heat Shrink Boots: Lipped,
Straight



TE Part #1623769-1
23E 2K2A 6X50PL B9 M10



TE Part #7-2213766-5
AV19 DPL 3A POWER LED GREEN 24V



TE Part #6-1437624-0
PKG50B1/4=KNOB PLASTIC 1/4 LEX



TE Part #800497-SF
FN9260-2-06



TE Part #1-1904045-5
V23333Z1001B045-EV-100

Documents

Product Drawings

M-SERIES KIT,V.35,34P

English

CAD Files

Customer View Model

ENG_CVM_CVM_213931-5_L.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_213931-5_L.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_213931-5_L.3d_igs.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_213931-5_K1.3d_igs.zip

English

Customer View Model

ENG_CVM_213931-5_K1.3d_stp.zip

English

Customer View Model

ENG_CVM_213931-5_K1.2d_dxf.zip

English

3D PDF

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

M_SERIES_PIN_AND_SOCKET_CONNECTORS

English