

| Art.-No.  | VE | PG  | EAN             |
|-----------|----|-----|-----------------|
| 227020018 | 1  | 131 | 4 008224 565820 |

POWERversal 9-way, 250V~, 16A, max.3600w, IP20, with illuminated switch (2-pole), with shutter, with 90° turned sockets, 65mm distance between sockets, mountable, reconnectable, cable H05VV-F3Gx1,5mm², 1,4m, length (lxbxh):(742,8x71x58,3)mm, silver-black



| Technical data                                   |               | 227020018 |
|--|---------------|-----------|
| Housing shape                                    | Rectangular   |           |
| Material   | Plastic       |           |
| Material quality                                 | Thermoplastic |           |
| Surface finishing                                | Matt          |           |
| Colour   | Silver        |           |
| Colour (user defined)                            | silver/black  |           |
| Degree of protection (IP)                        | IP20          |           |
| Angle rotated central insert                     | 90°           |           |
| Number of socket outlets with protective contact | 9             |           |
| Residual current circuit breaker (RCCB)          | No            |           |
| Mains filter                                     | No            |           |
| Over voltage protection                          | No            |           |
| Nominal current                                  | 16A           |           |
| Core cross section                               | 1.5mm²        |           |
| With cover                                       | No            |           |
| Transparent                                      | No            |           |
| Length of power cord                             | 1.4m          |           |
| Rotated central insert                           | Yes           |           |