



tesa® 4341

Product Information



High temperature masking tape for paint spraying followed by oven drying up to 140 °C

Product Description

tesa® 4341 is a slightly creped high temperature masking tape with excellent adhesive strength and highly durable tear-resistant properties. Due to its great flexibility and elasticity, this tape is perfect for professional varnish work on cars or motorbikes. The supple masking tape can withstand very high temperatures (up to 140 °C) and can also be used on tricky surfaces. It is also watertight and bonds well with varnishes and fillers. After oven drying, the high temperature masking tape is easy to remove.

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

- | | | | |
|--------------------|-----------------------|--|--------|
| • Backing material | slightly-creped paper | • Bio-based content of liner by weight (acc. EN 16785) | 55 % |
| • Type of adhesive | natural rubber | • Total thickness | 190 µm |

Properties/Performance Values

- | | |
|--------------------|---------|
| • Tensile strength | 53 N/cm |
|--------------------|---------|

Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit <http://l.tesa.com/?mp=04341>