

## Product datasheet

### Characteristics

## R9PCR

Resi9 XP - relay for mech ventilation



### Main

Range	Resi9
Product name	Resi9 XP RL
Product or component type	Control relay
Electrical circuit type	Control circuit
Poles description	1P + N

### Complementary

[In] rated current	5 A 250 V AC 50 Hz
Current consumption	100 mA 24 V AC 50 Hz
[Uc] control circuit voltage	24 V AC 50 Hz +/- 10 %
Hold-in power consumption in VA	0.5 VA
Inrush power in VA	0.5 VA
Signalling function	Start Test mode
Local signalling	Red indicator light on the front face
Colour	White (RAL 9003)
Auxiliary connection terminal	Tunnel type terminal 4 mm <sup>2</sup>
9 mm pitches	2
Height	81 mm
Width	18 mm
Depth	66 mm
Market segment	Residential

### Environment

ambient air temperature for operation	-20...50 °C
ambient air temperature for storage	-40...70 °C
standards	EN 60742 NFC 60-742

### Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 1742 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

### Contractual warranty

Warranty period	18 months
-----------------	-----------